



Project Number:			Tracking Code: TC08381976_ReportRev1				
Requested by: Bryon Saylor		Date: 1/26/2009 Product Rev: AP					
Part #: ESW-136-13-G-D/TSW-136-07-G-D			Lot #: 8/25/2008 Tech: Tony Wa		goner	Eng: Dave Scopelliti	
Part description: ESW/TSW						Qty to	test: 25
Test Start: 12/08/2009	Test Completed: 1/6	5/2009					

SAMTEC POWER CHARACTERIZATION





PART DESCRIPTION

ESW-136-13-G-D

Mated with

TSW-136-07-G-D



TC0838-ESW-1976
INITIAL RELEASE

CERTIFICATION

All instruments and measuring equipment were calibrated to National Institute for Standards and Technology (NIST) traceable standards according to ISO 10012-1 and ANSI/NCSL 2540-1, as applicable.

All contents contained herein are the property of Samtec. No portion of this report, in part or in full shall be reproduced without prior written approval of Samtec.

SCOPE

- 1. Temperature Rise/Current Carrying Capacity
 - 1.1. To determine the amount of current the device under test (DUT) can safely carry over the operating temperature range of the DUT.
 - 1.2. Contact loading will also be addressed in this document which will determine how much current can be carried as the number of energized contacts is varied.
- 2. Current Cycling
 - 2.1. To determine the performance of the device under test (DUT) when subjected to the power-on/power-off cycling that heats and cools the DUT in normal everyday use.
 - 2.2. Contact loading will set to 100% throughout the test.

APPLICABLE DOCUMENTS

Standards: EIA Publication 364-70 Temperature Rise

EIA Publication 364-06 Contact Resistance EIA Publication 364-55 Current Cycling TLPM-032 Current Carrying Capacity

TLPM-084 Current Cycling

IEC 512-3 Electromechanical Components for Electronic Equipment: Basic Testing Procedures

and Measuring Methods, Part 3: Current Carrying Capacity Tests

TEST SAMPLES AND PREPARATION

- 1) All materials shall be manufactured in accordance with the applicable product specification.
- 2) All test samples shall be identified and encoded to maintain traceability throughout the test sequences.
- 3) After soldering, the parts to be used shall be cleaned according to TLWI-0001.
- 4) All samples shall be visually inspected and cleaned as necessary.
- 5) Any additional preparation shall be noted in the individual test sequences.
- 6) Solder Information: Lead Free
- 7) Re-Flow Time/Temp: See accompanying profile.
- 8) All products designed to operate mounted on a printed circuits board shall be tested mounted to test boards in accordance with EIA-364-70.






Figure 1: Thermocouple placement shown; actual part not depicted.

- 9) The following loading configurations shall be tested for Temperature Rise/Current Carrying Capacity testing of single row connector systems:
 - a. One contact energized only
 - b. Two contacts energized adjacent to each other
 - c. Three contacts energized adjacent to each other
 - d. Four contacts energized adjacent to each other
 - e. All contacts energized
 - ★ Indicates energized contacts
- Indicates thermocouple monitored, energized contacts

Test Condition as in 9.1 above

+		

- 10) The following loading configurations shall be tested for Temperature Rise/Current Carrying Capacity testing of two row connector systems:
 - a. Two by One contact energized
 - b. Two by Two contacts energized adjacent to each other
 - c. Two by Three contacts energized adjacent to each other
 - d. Two by Four contacts energized adjacent to each other
 - e. All contacts energized

Test Condition as in 10.1 above

- ✦ Indicates energized contacts
- † Indicates thermocouple monitored, energized contacts

		
+		


11) For Current Cycling, only 100 % loading will be tested.



TC0838-ESW-1976
INITIAL RELEASE

OVEN PROFILE (Soldering Parts to Test Boards)

Standard Solder Paste Reflow Profile for Kester Paste Containing Alloys: Sn63Pb37 or Sn62Pb36Ag02





TC0838-ESW-1976 INITIAL RELEASE

FLOWCHARTS

Current Carrying Capacity

3 Mated Assemblies Each

TEST	GROUP A	GROUP B	GROUP C	GROUP D	GROUP E
STEP	3 Mated Assembies	3 Mated Assembies	3 Mated Assembies	3 Mated Assembles	3 Mated Assembies
	A CONTA CT POWERED	4 CONTA CES BOWERED	CONTACTS POWERED	6 CONTA CIES POWEDED	ALL CONTACTS DOWNEDED
	2 CONTACT POWERED	4 CONTACTS POWERED	6 CONTACTS POWERED	8 CONTACTS POWERED	ALL CONTACTS POWERED
01	CCC	CCC	CCC	CCC	CCC

(TIN PLATING) - Tabulate calculated current at RT, 65° C, 75° C and 95° C after derating 20% and based on 105° C

(GOLD PLATING) - Tabulate calculated current at RT, 85° C, 95° C and 115° C

after derating 20% and based on 125° C

CCC, Temp rise = EIA-364-70

Current Cycling

	GROUP A
TEST	8 Mated Assembies
STEP	ALL CONTACTS POWERED
	Current Cycle, 500 cycles at
01	125% of Rated current

Current Cycle = EIA 364-55, Condition "B", Method #4
Test at Current 125% of Rated Current

Measure at 45 minutes into ON time of cycle Measure Voltage Drop on 5 random contacts



TC0838-ESW-1976
INITIAL RELEASE

TEST PROCEDURES

Part No.	ESW-136-13-G-D	Mating Part No.	TSW-136-07-G-D		
Sample Size	15	Technician	Tony Wagoner		
Start Date	12/08/2009	Complete Date	12/08/2009		
Room Ambient	22.5°C	Relative Humidity	24%		
Fauinment ID# MO 04 DS 07 TC111307 (001 017)					

TEMPERATURE RISE (Current Carrying Capacity, CCC):

- 1) Thermocouples shall be calibrated in accordance with Samtec documents; TLWI 0003, Thermocouple Welding Procedure and TLWI 0005, Thermocouple Calibration
- 2) The thermocouples shall be placed at a location to sense the maximum temperature generated during testing.
- 3) Temperature stability shall be defined as the temperature at which three successive readings, 5 minutes apart, differ not more than 1° C (computer controlled data acquisition). This is the Temperature Rise that the Current Carrying Capacity and De-rating curves are based on.
- 4) The following loading configurations shall be tested (double for two row systems):
 - a. One contact energized only
 - b. Two contacts energized adjacent to each other
 - c. Three contacts energized adjacent to each other
 - d. Four contacts energized adjacent to each other
 - e. All contacts energized
- 5) The following loading configurations shall be tested for Temperature Rise/Current Carrying Capacity testing of two row connector systems:
 - a. Two by One contact energized
 - b. Two by Two contacts energized adjacent to each other
 - c. Two by Three contacts energized adjacent to each other
 - d. Two by Four contacts energized adjacent to each other
 - e. All contacts energized
- 6) Three samples shall be tested for each of the above configurations for a total of eighteen assemblies.
- 7) Temperature Rise measurements shall be made at 5 different current levels yielding temperature rises in the 10 to 70°C range.
- 8) The base curve for the Current Rating chart will be derived from the average (maximum) value of three test specimens in accordance with IEC 512-3, Test 5b.



TC0838-ESW-1976
INITIAL RELEASE

Part No.	ESW-136-13-G-D	Mating Part No.	TSW-136-07-G-D		
Sample Size	8	Technician	Tony Wagoner		
Start Date	12/08/2009	Complete Date	12/08/2009		
Room Ambient	26.1°C	Relative Humidity	22%		
Equipment ID#: PS-10, MO-09, TC010908-(060 - 077)					

CURRENT CYCLING

1. Samples shall be prepared and tested as above (paragraph 14.5).

2. Current Cycling shall be performed in accordance with EIA-364-55, Test Condition

3. Testing shall be as follows:

3.1. Test Current: **2.5**(125% of 30°C Rating)

3.2. "ON" Time: 45 Minutes 3.3. "OFF" Time: 15 Minutes

3.4. Number of Cycles: 500

3.5. Measurements: 40 minutes into ON cycle

3.5.1. Temperature

3.5.2. Voltage Drop/Contact Resistance

4. Temperature vs. Number of Cycles and Voltage Drop vs. Number of Cycles shall be measured and recorded.



TC0838-ESW-1976
INITIAL RELEASE

TEST RESULTS

CURRENT CARRYING CAPACITY (CCC) RESULTS

- There was no evidence of physical damage to the test samples as tested.
- The following is a summary of the observed data:

Temperature Rise, CCC at a 20% de-rating

- CCC for a 30°C Temperature Rise------5.2A per contact with 2 contacts (2 x 1) powered
- CCC for a 30°C Temperature Rise ------4.5A per contact with 4 contacts (2 x 2) powered
- CCC for a 30°C Temperature Rise------3.5A per contact with 6 contacts (2 x 3) powered
- CCC for a 30°C Temperature Rise------3.1A per contact with 8 contacts (2 x 4) powered
- CCC for a 30°C Temperature Rise -----2.0A per contact with 72 contacts (2 x 36) powered

CURRENT CYCLING RESULTS

Test Condition: 500 Cycles, 45 minutes ON and 15 minutes OFF


- Contact Resistances, Measured 40 minutes into the FIRST and LAST ON cycle
 - Initial
 - Min ----- 3.67 mOhms
 - Max------4.45 mOhms
 - o Final
 - Min ----- 3.62 mOhms
 - Max------4.40 mOhms
- Temperature Change, Measured 40 minutes into the FIRST and LAST ON cycle
 - o Initial Temperature Change ------30.0°C
 - Final Temperature Change ------29.4°C

TC0838-ESW-1976
INITIAL RELEASE

TEST DATA

CONTACT RESISTANCE @ RATED CURRENT

The following data represents the Voltage drop and Contact Resistance at Rated Current for the 100% energized samples:



CONTACT RESISTANCE DATA ALL CONTACTS ENERGIZED (mΩ)						
TEST CURRENT AMPS	1.41	1.99	2.44	2.81	3.14	
Min	3.63	3.61	3.63	3.67	3.68	
Max	4.4	4.4	4.43	4.49	4.52	
Avg	3.99	3.98	4.01	4.06	4.08	




TC0838-ESW-1976
INITIAL RELEASE

TEST DATA

VOLTAGE DROP @ RATED CURRENT


The following data represents the Voltage drop at Rated Current for the 100% energized samples:



VOLTAGE DROP DATA ALL CONTACTS ENERGIZED (mV)						
TEST CURRENT AMPS	1.41	1.99	2.44	2.81	3.14	
Min	5.12	7.19	8.86	10.32	11.56	
Max	6.2	8.75	10.8	12.63	14.18	
Avg	5.66	7.97	9.83	11.47	12.88	



TC0838-ESW-1976
INITIAL RELEASE




TEMPERATURE RISE DATA TWO CONTACT ENERGIZED (Degrees Celsius above ambient)					
TEST CURRENT AMPS	3.14	4.44	5.45	6.29	7.03
Sample 1	7.5	14.1	20.5	26.7	32.2
Sample 2	8.2	15.7	23	30.2	37.1
Sample 3	8	15.2	22.2	29.1	35.7
Min	7.5	14.1	20.5	26.7	32.2
Max	8.2	15.7	23	30.2	37.1
Avg	7.9	15	21.9	28.67	35

Ambient Temperature, ° C

→ Indicates energized contacts


→ Indicates thermocouple monitored, energized contacts

Double Row Configuration






TC0838-ESW-1976 INITIAL RELEASE



TEMPERATURE RISE DATA FOUR CONTACTS ENERGIZED (Degrees Celsius above ambient)						
TEST CURRENT AMPS	3.14	4.44	5.45	6.29	7.03	
Sample 4	11.3	21.3	31.1	40.4	49.6	
Sample 5	10.6	19.4	28	36.3	44	
Sample 6	9.9	18.2	27.3	35.5	43.2	
Min	9.9	18.2	27.3	35.5	43.2	
Max	11.3	21.3	31.1	40.4	49.6	
Avg	10.6	19.63	28.8	37.4	45.6	


♣ Indicates energized contacts

→ Indicates thermocouple monitored, energized contacts





TC0838-ESW-1976 INITIAL RELEASE



TEMPERATURE RISE DATA SIX CONTACTS ENERGIZED (Degrees Celsius above ambient)						
TEST CURRENT AMPS	2.43	3.44	4.22	4.87	5.45	
Sample 7	10.2	19.6	28.6	36.8	45.5	
Sample 8	10.2	19.6	28.5	37.1	46.2	
Sample 9	9.3	17.7	25.8	33.6	41.7	
Min	9.3	17.7	25.8	33.6	41.7	
Max	10.2	19.6	28.6	37.1	46.2	
Avg	9.9	18.97	27.63	35.83	44.47	


♣ Indicates energized contacts

igspace Indicates thermocouple monitored, energized contacts

*			
*	+	*	



TC0838-ESW-1976 INITIAL RELEASE




TEMPERATURE RISE DATA EIGHT CONTACTS ENERGIZED (Degrees Celsius above ambient)						
TEST CURRENT AMPS	2.43	3.44	4.22	4.87	5.45	
Sample 10	13	25.3	37	48	58.8	
Sample 11	12.1	23.4	34.2	44.3	55	
Sample 12	11.8	23	33.6	43.6	54.1	
Min	11.8	23	33.6	43.6	54.1	
Max	13	25.3	37	48	58.8	
Avg	12.3	23.9	34.93	45.3	55.97	

14 of 21

- ♣ Indicates energized contacts
- → Indicates thermocouple monitored, energized contacts


			
	*	+	*






TEMPERATURE RISE DATA ALL CONTACTS ENERGIZED (Degrees Celsius above ambient)								
TEST CURRENT AMPS								
Sample 13	10.8	20	28.6	37	44.7			
Sample 14	11	20	28.8	37.3	45.1			
Sample 15	10.4	18.9	27.4	35.4	42.7			
Min	10.4	18.9	27.4	35.4	42.7			
Max	11	20	28.8	37.3	45.1			
Avg	10.73	19.63	28.27	36.57	44.17			

- ♣ Indicates energized contacts
- → Indicates thermocouple monitored, energized contacts









TEMPERATURE RISE DATA ALL CONTACTS ENERGIZED (Degrees Celsius above ambient)						
	INITIAL	50 CYCLES	100 CYCLES	200 CYCLES	500 CYCLES	
Min	28.4	28	28.3	28	27.4	
Max	32.8	32.9	33.3	33	32.5	
Avg	30	29.8	30.2	29.8	29.4	





CONTACT RESISTANCE DATA ALL CONTACTS ENERGIZED (mΩ)						
	INITIAL	50 CYCLES	100 CYCLES	200 CYCLES	500 CYCLES	
Min	3.67	3.64	3.64	3.63	3.62	
Max	4.45	4.42	4.42	4.41	4.4	
Avg	4.04	4.01	4.01	4	3.99	





VOLTAGE DROP DATA ALL CONTACTS ENERGIZED (MV)						
	INITIAL	50 CYCLES	100 CYCLES	200 CYCLES	500 CYCLES	
Min	9.18	9.11	9.09	9.08	9.06	
Max	11.12	11.05	11.04	11.03	11.01	
Avg	10.1	10.03	10.02	10	9.99	



TC0838-ESW-1976
INITIAL RELEASE

EQUIPMENT AND CALIBRATION SCHEDULES

Equipment #: PS-01

Description: System Power Supply **Manufacturer:** Hewlett Packard

Model: HP 6033A

Serial #: (HP) 3329A-07330 Accuracy: See Manual

... Last Cal: 06/16/2008, Next Cal: 06/17/2009

Equipment #: PS-02

Description: System Power Supply, 0 - 20V/ 0 - 30 amp, 200 Watts

Manufacturer: Hewlett Packard

Model: 6033A

Serial #: (HP) 2847A-04167 Accuracy: See Manual

... Last Cal: 04/07/2008, Next Cal: 04/07/2009

Equipment #: PS-03

Description: Power Supply, 50 amp

Manufacturer: HP/Agilent

Model: 0-60V / 0 - 50 amps / 1000 Watts

Serial #: 2723A-02144 Accuracy: See Manual

... Last Cal: 06/16/2008, Next Cal: 06/16/2009

Equipment #: PS-04

Description: 60 V, 50 A DC Power Supply - AutoRanging SO

Manufacturer: Hewlett Packard / Agilent

Model: AT-6032A Serial #: MY41001186

Accuracy: See Manual Current Cycle Chamber 2 - Lower Shelf

... Last Cal: 06/16/2008, Next Cal: 06/16/2009

Equipment #: PS-05

Description: 60 V, 50 A DC Power Supply - AutoRanging SO

Manufacturer: Hewlett Packard / Agilent

Model: AT-6032A **Serial #:** MY41001158

Accuracy: See Manual Current Cycle Chamber 2 - Lower Shelf

... Last Cal: 06/16/2008, Next Cal: 06/16/2009

Equipment #: PS-06

Description: 60 V, 50 A DC Power Supply - AutoRanging SO

Manufacturer: Hewlett Packard / Agilent

Model: AT-6032A **Serial #:** US35420827

Accuracy: See Manual Current Cycle Chamber 3 (This chamber only has 1 shelf)

... Last Cal: 06/16/2008, Next Cal: 06/16/2009



TC0838-ESW-1976 INITIAL RELEASE

Equipment #: PS-07

Description: 20 V, 120 A DC Power Supply - AutoRanging SO/HPIB

Manufacturer: Hewlett Packard / Agilent

Model: AT-6031A **Serial #:** 2721A00648

Accuracy: See Manual See Manual

... Last Cal: 06/16/2008, Next Cal: 06/16/2009

Equipment #: PS-09

Description: 60 V, 50 A DC Power Supply - AutoRanging SO

Manufacturer: Hewlett Packard / Agilent

Model: AT-6032A **Serial #:** US38322853

Accuracy: See Manual Current Cycle Chamber 3 (This chamber only has 1 shelf)

... Last Cal: 10/21/2008, Next Cal: 10/21/2009

Equipment #: PS-10

Description: 60 V, 50 A DC Power Supply - AutoRanging SO

Manufacturer: Hewlett Packard / Agilent

Model: AT-6031A **Serial #:** 3440A10457

Accuracy: See Manual See Manual

... Last Cal: 10/21/2008, Next Cal: 10/21/2009

Equipment #: MO-02

Description: Multimeter /Data Acquisition System

Manufacturer: Keithley

Model: 2700 Serial #: 0780546 Accuracy: See Manual

... Last Cal: 07/08/2008, Next Cal: 07/08/2009

Equipment #: MO-08

Description: Model 2750 Multimeter/Switch System (Integra Series)

Manufacturer: Keithley

Model: 2750

Serial #: WDC-875194 Accuracy: See Manual

... Last Cal: 11/24/2008, Next Cal: 11/24/2009

Equipment #: MO-09

Description: Model 2750 Multimeter/Switch System (Integra Series)

Manufacturer: Keithley

Model: 2750

Serial #: WDC-874817 Accuracy: See Manual

... Last Cal: 11/24/2008, Next Cal: 11/24/2009



TC0838-ESW-1976
INITIAL RELEASE

Equipment #: TC111307-(001 - 017)

Description: CCC Chamber Thermocouples

Manufacturer: Samtec

Model:

Serial #: TC111307-(001 - 017)

Accuracy: +/- 1 Deg.

... Last Cal: 11/03/2008, Next Cal: 11/03/2009

Equipment #: TC111307-(041 - 059)

Description: Current Cycling Chamber #1 Thermcouples

Manufacturer: Samtec

Model:

Serial #: TC111307-(041 - 059)

Accuracy: +/- 1 Deg.

... Last Cal: 11/03/2008, Next Cal: 11/03/2009

Equipment #: TC010908-(060 - 077)

Description: Current Cycling Chamber # 2 Thermcouples

Manufacturer: Samtec

Model:

Serial #: TC010908-(060-077)

Accuracy: +/- 1 Deg.

... Last Cal: 11/03/2008, Next Cal: 11/03/2009

Equipment #: TC111307-(118 - 136)

Description: Current Cycling Chamber # 3 Thermcouples

Manufacturer: Samtec

Model:

Serial #: TC111307-(118 - 136)

Accuracy: +/- 1 Deg.

... Last Cal: 11/03/2008, Next Cal: 11/03/2009

Equipment #: TC120607-(101C - 109C), 110807-140 **Description:** Current Cycling Chamber # 4 Thermcouples

Manufacturer: Samtec

Model:

Serial #: TC120607-(101C - 109C), 110807-140

Accuracy: +/- 1 Deg.

... Last Cal: 12/06/2008 & 11/08/2008, Next Cal: 12/06/2009 & 11/08/2009